

Data sheet

6GF3560-8EA02-0FF0

product type designation

product description

MV500 C-mount lens 16 mm

C mount lens, 16 mm focal distance, aperture 1:1.8 manually adjustable

MV560 fixed-focus lens 16 mm only for MV560 devices MLFB: 6GF3560-0LE10; focal length 16 mm; adjustable aperture; scope of delivery: lens a. 15 mm protective barrel extender important: no built-in ring lamp can be used.



suitability for use

Swappable lens with C-mount connection

suitability for operation

lens for MV500

mechanical data

color

black

ambient conditions

ambient temperature

- during operation
- during storage
- during transport

0 ... 50 °C
-30 ... +70 °C
-30 ... +70 °C

design, dimensions and weights

height

60 mm

diameter

39 mm

net weight

175 g

further information / internet links

internet link

- to website: TIA Selection Tool
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Selection guide for cables and connectors
- to website: Image database
- to website: CAX-Download-Manager
- to website: Industry Online Support

<http://www.siemens.com/tia-selection-tool>
<http://www.siemens.com/codereader>
<https://mall.industry.siemens.com>
<http://www.siemens.com/industry/infocenter>
<https://sie.ag/2QdlxcP>
<http://automation.siemens.com/bilddb>
<http://www.siemens.com/cax>
<https://support.industry.siemens.com>

last modified:

5/28/2023 