

SITRANS FM MAG 3100 Full-bore electromagnetic flow sensor, flanged, diameter DN 15 to DN 2000 (1/2" to 78"). Suitable for volume flow measurement of liquids (conductive), main applications in process industry, chemical industry, steel industry, mining, utility, power generation and distribution, O&G/HPI. . DN40, 1 1/2 Inch EN1092-1, PN40 Carbon steel flanges ASTM A 105, corrosion-resistant coating of category C4 Soft Rubber Stainless steel AISI 316Ti / 1.4571 (not for PFA) Sensor for remote transmitter (Order transmitter separately) No bus communication Metric Polyamid terminal box or 6000 I compact.

Further information

Industry Online Support (Manuals, Catalogs, Certificates, FAQ, ...)

<https://support.industry.siemens.com/cs/products?mfn=ps&lc=en-WW>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com>

