

product type designation

product description



Distance piece MDS D160 / MDS D460

Support for mounting transponders with 16 mm diameter and 10 mm distance to metal

MOBY D/RF300 ISO Spacer for MDS D160/MDS D460; Packing unit = Minimum order quantity: 50 units.

suitability for use

Support is mounted with an M4 countersunk head screw, the transponder is snapped on

suitability for operation

for transponders MDS D160/D460

mechanical data

material

PA 6.6 GF

color

black

ambient conditions

ambient temperature

- during operation -25 ... +85 °C
- during storage -25 ... +100 °C
- during transport -25 ... +100 °C

design, dimensions and weights

height

14 mm

diameter

20 mm

further information / internet links

internet link

- to website: TIA Selection Tool <http://www.siemens.com/tia-selection-tool>
- to the website: IWLAN <http://www.siemens.com/iwlan>
- to website: Industrial communication <http://www.siemens.com/ident/rfid>
- to website: Industry Mall <https://mall.industry.siemens.com>
- to website: Information and Download Center <http://www.siemens.com/industry/infocenter>
- to website: Selection guide for cables and connectors <https://sie.ag/2QdlxcP>
- to website: Image database <http://automation.siemens.com/bilddb>
- to website: CAx-Download-Manager <http://www.siemens.com/cax>
- to website: Industry Online Support <https://support.industry.siemens.com>

last modified:

5/28/2023