

## Data sheet

6GT2690-0AK00

### product type designation

product description



### Distance piece MDS D124/D324/D424/RF320T

Support for mounting transponders with 27 mm diameter and 15 mm distance to metal

MOBY D/RF300 ISO/RF200 Spacer for MDS D124/D324/D424/D524 and RF320T  
Temperature range up to +180 °C Packing unit = Minimum order quantity: 20 units.

suitability for use

Support is mounted with an M4 countersunk head screw, the transponder is snapped on

suitability for operation

for transponders RF320T MDS D124/D324/D424

### mechanical data

material

PPS

color

black

### ambient conditions

ambient temperature

- during operation -25 ... +180 °C
- during storage -40 ... +180 °C
- during transport -40 ... +180 °C

### design, dimensions and weights

height

22 mm

diameter

36 mm

### further information / internet links

internet link

- to website: TIA Selection Tool <http://www.siemens.com/tia-selection-tool>
- to the website: IWLAN <http://www.siemens.com/iwlan>
- to website: Industrial communication <http://www.siemens.com/ident/rfid>
- to website: Industry Mall <https://mall.industry.siemens.com>
- to website: Information and Download Center <http://www.siemens.com/industry/infocenter>
- to website: Selection guide for cables and connectors <https://sie.ag/2QdlxcP>
- to website: Image database <http://automation.siemens.com/bilddb>
- to website: CAX-Download-Manager <http://www.siemens.com/cax>
- to website: Industry Online Support <https://support.industry.siemens.com>

last modified:

5/28/2023 