6ES7900-1AA00-0XA0

Data sheet

IEC cable, Germany 230V AC, angled Socket, for Germany; France; Spain; The Netherlands; Belgium; Sweden; Austria; Finland for devices with corresponding interface Further information, Quantity and content: see technical data



General information	
Product type designation	Cable for non-heating apparatus
Interfaces	
Interfaces/bus type	Line-side, country-specific connector: Type CEE 7/7 Schuko
Device-side interface	
 Number of pins device-side 	3; Female, C13 connector type
Standards, approvals, certificates	
CE mark	Yes
CSA approval	Yes; N11419
KC approval	Yes; KTL SW04001-6001
EAC (formerly Gost-R)	Yes
CCC	Yes
RoHS conformity	Yes
Ambient conditions	
Suited for indoor use	Yes; Max. 10 A
Ambient temperature during operation	
• min.	-10 °C
• max.	50 °C
Ambient temperature during storage/transportation	
• min.	-20 °C
• max.	85 °C
Relative humidity	
Operation, max.	90 %
Cables	
Cable length	3 m
Color of cable sheath	Black
Weights	
Weight, approx.	290 g
Scope of supply	
Delivery quantity in pieces	1; AC cable for DE, FR, ES, NL, BE, SE, AT, FI
Other	
Merchandise	Yes; VII-H05VVF3G100-C13W/3,00M SW9005 (L53)
Manufacturer name	FELLER GmbH
Manufacturer's address	Wärndorferstraße 3, 2525 Günselsdorf, Austria; email: sales@feller-at.com
Target devices	Suitable for all appropriate DC interfaces
Note:	http://www.feller-at.com
Usable in the following products	
Product 1	6AV6671-5CN00-0AX3
last modified:	4/19/2023 🗗

