

IEC cable, Switzerland 230V AC, angled, for IPC and power supplies Further information, Quantity and content: see technical data



General information	
Product type designation	Cable for non-heating apparatus
Interfaces	
Interfaces/bus type	Line-side, country-specific connector: Type J (SEV 1011)
Device-side interface	
<ul style="list-style-type: none"> Number of pins device-side 	3; Female, C13 connector type
Standards, approvals, certificates	
CE mark	Yes
CSA approval	Yes; N11419
KC approval	No
EAC (formerly Gost-R)	No
CCC	Yes
RoHS conformity	Yes
Ambient conditions	
Suited for indoor use	Yes; Max. 10 A
Ambient temperature during operation	
<ul style="list-style-type: none"> min. max. 	-10 °C 50 °C
Ambient temperature during storage/transportation	
<ul style="list-style-type: none"> min. max. 	-20 °C 85 °C
Relative humidity	
<ul style="list-style-type: none"> Operation, max. 	90 %
Cables	
Cable length	3 m
Color of cable sheath	Black
Weights	
Weight, approx.	260 g
Scope of supply	
Delivery quantity in pieces	1; AC cable for CH
Other	
Merchandise	Yes; 12G-H05VVF3G100-C13W/3,00M SW9005
Manufacturer name	FELLER GmbH
Manufacturer's address	Wärndorferstraße 3, 2525 Günselsdorf, Austria; email: sales@feller-at.com
Target devices	Suitable for all appropriate DC interfaces
Note:	http://www.feller-at.com
Usable in the following products	
<ul style="list-style-type: none"> Product 1 	6AV6671-5CN00-0AX3

last modified:

4/19/2023

