

IEC cable, USA, 230V AC, angled, for IPC and power supplies Further information, Quantity and content: see technical data



| General information | |
|--|---|
| Product type designation | Cable for non-heating apparatus |
| Interfaces | |
| Interfaces/bus type | Line-side, country-specific connector: Type B (NEMA 5-15) |
| Device-side interface | |
| <ul style="list-style-type: none"> Number of pins device-side | 3; Female, C13 connector type |
| Standards, approvals, certificates | |
| CE mark | Yes |
| CSA approval | Yes; H |
| KC approval | Yes; KTL SW04012-11002 |
| EAC (formerly Gost-R) | No |
| CCC | No |
| RoHS conformity | Yes |
| Ambient conditions | |
| Suited for indoor use | Yes; Max. 10 A |
| Ambient temperature during operation | |
| <ul style="list-style-type: none"> min. max. | -10 °C 50 °C |
| Ambient temperature during storage/transportation | |
| <ul style="list-style-type: none"> min. max. | -20 °C 85 °C |
| Relative humidity | |
| <ul style="list-style-type: none"> Operation, max. | 90 % |
| Cables | |
| Cable length | 3 m |
| Color of cable sheath | Black |
| Weights | |
| Weight, approx. | 230 g |
| Scope of supply | |
| Delivery quantity in pieces | 1; AC cable for US |
| Other | |
| Merchandise | Yes; 498G-SVT3X18AWG-C13W/3,00M SW9005 (GNSWWS) |
| Manufacturer name | FELLER GmbH |
| Manufacturer's address | Wärndorferstraße 3, 2525 Günselsdorf, Austria; email: sales@feller-at.com |
| Target devices | Suitable for all appropriate DC interfaces |
| Note: | http://www.feller-at.com |
| Usable in the following products | |
| <ul style="list-style-type: none"> Product 1 | 6AV6671-5CN00-0AX3 |

last modified:

4/19/2023

