

SITRANS LR560 Radar level transmitter with flush lens antenna: continuous, non-contact, 100 m (328 ft) range, for general solids applications. Measurement and process temperature range: 40m (131 ft) max range, -40 C degrees to +100 C degrees Process connection: Universal flat-faced flange fits ANSI/DIN/JIS flanges: 3" / 80 mm, painted aluminum, with integral aimer Enclosure (with cable inlet): Stainless Steel, 1 X 1/2" NPT . Label: Sitrans LR560 Pressure Rating: 0.5 bar g (7.5 psi g) maximum Output/communication: 4 to 20 mA, HART Approvals: Ordinary Locations/General Purpose (Non-Ex), FM, cCSAus, IC, FCC, CE, UKCA, RED, RCM Local display interface: With LDI (local display interface)

Further information

Industry Online Support (Manuals, Catalogs, Certificates, FAQ, ...)

<https://support.industry.siemens.com/cs/products?mf=ps&lc=en-WW>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com>

