

protective film 12"; front, type 6, for Industrial Flat Panel Basic further information, quantity and content: see technical specifications

| General information | |
|---|---|
| Product type designation | protective film 12" type 6 |
| Installation type/mounting | |
| Mounting in portrait format possible | Yes |
| Mounting in landscape format possible | Yes |
| Standards, approvals, certificates | |
| CE mark | No; No CE marking obligation |
| Ambient conditions | |
| Suited for indoor use | Yes |
| Suited for outdoor use | Yes; only suitable under certain conditions due to different environmental conditions; replacement cycle can be increased |
| Ambient temperature during operation | |
| • min. | -40 °C |
| • max. | 80 °C |
| Ambient temperature during storage/transportation | |
| • min. | -40 °C |
| • max. | 80 °C |
| Relative humidity | |
| • Operation, max. | 90 % |
| • Condensation permissible | No |
| Mechanics/material | |
| Material | |
| • Plastic | Yes; Autoflex EB Antiglare |
| Enclosure material (front) | |
| • Plastic | Yes; resistant to alcohols, diluted acids, diluted alkali, esters, hydrocarbons, ketones and household cleaners |
| Dimensions | |
| Width | 311 mm |
| Height | 217 mm |
| Thickness | 0.2 mm |
| Scope of supply | |
| Delivery quantity in pieces | 10; Units per set |
| Other | |
| printable with laser printer | No |
| Merchandise | Yes |
| Manufacturer name | Kolb-Siebdruck GmbH & Co. KG |
| Manufacturer's address | Espenstraße 5, 95632 Wunsiedel, Germany |
| Note: | edge-adhesive, cannot be trimmed, for resistive touch systems or membrane fronts |

last modified:

9/19/2021 