

protective film 22"; front, type 6, for Industrial Flat Panel Basic further information, quantity and content: see technical specifications

General information	
Product type designation	Protective film 22" type 6
Installation type/mounting	
Mounting in portrait format possible	Yes
Mounting in landscape format possible	Yes
Standards, approvals, certificates	
CE mark	No; No CE marking obligation
Ambient conditions	
Suited for indoor use	Yes
Suited for outdoor use	Yes; only suitable under certain conditions due to different environmental conditions; replacement cycle can be increased
Ambient temperature during operation	
• min.	-40 °C
• max.	80 °C
Ambient temperature during storage/transportation	
• min.	-40 °C
• max.	80 °C
Relative humidity	
• Operation, max.	90 %
• Condensation permissible	No
Mechanics/material	
Material	
• Plastic	Yes; Autoflex EB Antiglare
Enclosure material (front)	
• Plastic	Yes; resistant to alcohols, diluted acids, diluted alkali, esters, hydrocarbons, ketones and household cleaners
Dimensions	
Width	531 mm
Height	326 mm
Thickness	0.2 mm
Scope of supply	
Delivery quantity in pieces	10; Units per set
Other	
printable with laser printer	No
Merchandise	Yes
Manufacturer name	Kolb-Siebdruck GmbH & Co. KG
Manufacturer's address	Espenstraße 5, 95632 Wunsiedel, Germany
Note:	edge-adhesive, cannot be trimmed, for resistive touch systems or membrane fronts

last modified:

9/19/2021 