



SIMATIC S7-1500 / ET 200MP; slot cover for the active backplane bus of S7-1500 for protection against ESD and for mechanical fixing on the S7-1500 mounting rail. unused slots must be provided with a slot cover! 5 units per packing unit

General information	
Product type designation	Slot cover
Degree and class of protection	
IP degree of protection	IP20
Ambient conditions	
Ambient temperature during operation	
• min.	-30 °C
• max.	60 °C
• horizontal installation, min.	-30 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-30 °C
• vertical installation, max.	40 °C
Ambient temperature during storage/transportation	
• min.	-40 °C
• max.	70 °C
Air pressure acc. to IEC 60068-2-13	
• Operation, min.	795 hPa
• Operation, max.	1 040 hPa
• Storage/transport, min.	660 hPa
• Storage/transport, max.	1 140 hPa
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	5 000 m
Relative humidity	
• Operation at 25 °C without condensation, max.	95 %
Dimensions	
Width	25 mm
Height	150 mm
Depth	32 mm

last modified: 3/26/2021 