

spare key PRO, type 14 for key-operated switch PRO further information, quantity and content: see technical specifications



Figure similar

General information	
Product type designation	Spare key
Standards, approvals, certificates	
CE mark	No; No CE marking obligation
Ambient conditions	
Ambient temperature during operation	
• min.	-40 °C
• max.	80 °C
Ambient temperature during storage/transportation	
• min.	-40 °C
• max.	80 °C
Relative humidity	
• Operation, max.	90 %
Mechanics/material	
Material	
• Sheet steel	Yes
Dimensions	
Width	15 mm; Approximate dimension
Height	35 mm; Approximate dimension
Thickness	4 mm
Weights	
Weight (without packaging)	5 g
Scope of supply	
Delivery quantity in pieces	6; 3 pairs
Other	
Merchandise	Yes; RAFI 9.30.275.005/0000
Manufacturer name	RAFI GmbH & Co.KG
Manufacturer's address	Ravensburger Str. 128-134, 88276 Berg, Germany
Target devices	6AV7674-1ME00-0AA0
Usable in the following products	
• Product 1	6AV7674-1ME00-0AA0

last modified: 5/19/2021 