

Product fiche

Delegated Regulation (EU) 812/2013

Supplier name or trademark	SYGONIX
Model identifier	2886555
Declared load profile	XXS
Water heating energy efficiency class	A
Water heating energy efficiency	37 %
Annual electricity consumption	496 kWh
Annual fuel consumption	- GJ
Other Information	
Thermostat temperature settings	No setting
Sound power level (Indoors)	15 dB
Specific precautions	<ol style="list-style-type: none">1. Erect product vertically, avoid tilting or upside-down installation.2. Connect water source before power supply during first use and after water cut-off.3. Do not use electricity when water in appliance is frozen.4. Do not install appliance outdoors or in freezing areas.5. Maximum water temperature is 50°C when in use.6. Do not cover plug, socket, or appliance with towels or other items. Do not use wet hands to pull the plug.7. Do not use with other high-power appliances when power capacity is low.8. Outlet must only be connected to specified faucet or connector, no choke element.9. Descale spray cap regularly.10. Ground appliances.11. Replace damaged power cord with professional personnel.12. Permanently connect appliance to fixed wiring with fully disconnected device under voltage grade III.13. Maximum inlet pressure is 0.4 MPa, minimum is 0.04 MPa.14. Disconnect power when not in use for safety.

Model placed on the Union market from 04/07/2023.



EPREL registration number: 1642700

<https://eprel.ec.europa.eu/qr/1642700>

Supplier: Conrad Electronic SE (Importer)

Website:

Customer care service:

Name: Conrad Electronic SE

Website:

Email: product.support@conrad.de

Phone: 09622300

Address:

Klaus-Conrad-Str. 1
92240 Hirschau
Germany