



# LogiLink®

## EV Charging Cable

Type 2, 3-Phase, with Protection Bag

Art. No.: EVC0120–EVC0125

LogiLink Type 2 standard charging cables connect your EV to the charging station, charging pole or wall-box, for easy charging at home or on the road. Suitable for plug-in hybrid (PHEV) and battery electric vehicles (BEV).

### Features:

- » Suitable for electric vehicles (BEV) and plug-in hybrids (PHEV) from Tesla, Audi, Mercedes-Benz, BMW, VW, Porsche, Renault, Citroen, Peugeot, Ford, Opel, Chrysler, General Motors and others that have a CCS or Type 2 charging connection
- » Charging mode according to Mode 3 (IEC 61851) and connector according to IEC 62196-2
- » CE & TUV certified
- » IP65 with protection cap and overrun protections



## Specifications:

Connector 1	IEC 62196-2 Type 2 charging plug, male
Connector 2	IEC 62196-2 Type 2 charging plug, female
Charging Mode	Mode 3
Nominal Voltage	480 V AC
Nominal Frequency	50 Hz/60 Hz
Connection	3-Phase
Housing Protection Type	Mated: IP65, Unmated: IP54
Cable Type	H07BZ5-F 5*6.0 mm <sup>2</sup> +1*0.5 mm <sup>2</sup>
Working Temperature	-30–50°C
Housing Material	Plastic
Color	Black
Standard	IEC 62196-2, EN 50620:2017/A1:2019, IEC 61851, IEC 60332-1-2, EN 60811-404, IEC 60754-2, IEC 60068-2-5

Art-No.	Charging Power	Charging Current	Cable Length	EAN Code
EVC0120	22 kW	32 A	2.5 m	4052792070217
EVC0121	22 kW	32 A	5 m	4052792070224
EVC0122	22 kW	32 A	7.5 m	4052792070231
EVC0123	22 kW	32 A	10 m	4052792070248
EVC0124	11 kW	16 A	5 m	4052792070255
EVC0125	11 kW	16 A	7.5 m	4052792070262

## Package Contents:

- » 1 x EV Charging Cable
- » 1 x Protection Bag
- » 1 x User Manual



## Package Information:

Art-No.	Packing Dimension	Packing Weight	Carton Dimension	Carton Q'ty	Carton Weight
EVC0120	360 x 360 x 90 mm	2.37 kg	380 x 380 x 380 mm	4 pcs	11.2 kg
EVC0121	360 x 360 x 90 mm	3.7 kg	380 x 380 x 380 mm	4 pcs	15.6 kg
EVC0122	360 x 360 x 120 mm	4.9 kg	380 x 380 x 380 mm	3 pcs	15.5 kg
EVC0123	360 x 360 x 120 mm	6.02 kg	380 x 380 x 380 mm	3 pcs	18.9 kg
EVC0124	360 x 360 x 90 mm	2.6 kg	380 x 380 x 380 mm	4 pcs	11.2 kg
EVC0125	360 x 360 x 90 mm	3.3 kg	380 x 380 x 380 mm	3 pcs	10.7 kg



\*The specifications and pictures are subject to change without prior notice.  
\*All trade names referenced are the registered trademarks of their respective owners.

Made in China