

WALL SCANNER & MULTI-DETECTOR

ALLOWS THE DETECTION OF STRUCTURES IN WALLS, WALL SURFACES OR FLOORS



With our wall scanner & multi-detector you can easily and safely detect structures in drywall, walls, wall surfaces or floors.

Thanks to the innovative sensor technology, the device can locate not only live wires, but also metals and wooden substructures with pinpoint accuracy.

With its three modes, it is versatile and offers a maximum detection depth of up to 120 mm. The clear display shows exactly what is behind the wall, while the three-color LED illuminated ring provides additional visual feedback.

A circular case opening makes it easy to mark the exact location of the find, and for optimal handling, the device is supplied with a practical protective case.

MAIN FEATURES	
Special functions	Detection of metal, wood and live wires
	Three-color LED illuminated ring
	Acoustic warning signal
	Straightforward display
	Circular case opening for easy marking
Maximum detection depth	Ferrous metals: 120 mm
	Non ferrous metals (copper): 100 mm
	Live wires: (230 V): 50 mm
	Single strand copper wire: 40 mm
	Wood: 20 mm (Precision mode) or 38 mm (Depth mode)
Automatic shutdown	After about 5 minutes

TECHNICAL SPECIFICATIONS		
Battery specifications	3,7 V - 300 mAh - LI-ION	
Operating time	ca. 2 h	
Battery charging option	USB-C	
Operating temperature	-10 °C - 50 °C	
Storage temperature	-20 °C - 70 °C	

ADDITIONAL INFORMATIO	N
Dimensions	138 x 68 x 22 mm
Article No.	JT-Line01
Items shipped	Multi-detector, protective bag, USB-C cable
Customs tariff no.	90318080
EAN	4250236826134

Published: 2023.06.05