

REVOLUTION PI

RevPi Connect 4

Technical Data


Article No.: 100376 (2 GB / 8 GB)

Article No.: 100377 (WLAN / 2 GB / 8 GB)

Article No.: 100378 (4 GB / 32 GB)

Article No.: 100379 (WLAN / 4 GB / 32 GB)

Article No.: 100380 (WLAN / 8 GB / 32 GB)



Housing dimensions (H x W x D)	96 x 45 x 110,5 mm
Housing type	DIN rail housing (for DIN rail version EN 50022)
Housing material	Polycarbonate
Weight	approx. 197 g / 224 g (incl. connectors)
Protection class	IP20
Power supply	10.8 ... 28.8 V DC ¹
Max. power consumption	20 W (incl. 2 x 900 mA USB load) ²
Allowable operating temperature	-25 ... +55 °C
Allowable storage temperature	-40 ... +85 °C
Max. relative humidity (at 40 °C)	up to 93 % (non-condensing)
Interfaces	2 x USB A 3.2 Gen 1 2x RJ45 GBit Ethernet 1 x RS485 screw-type terminal 1 x Micro-USB (solely for image transfer to eMMC) 1 x Micro-HDMI 2.0a (4K) 2 x PiBridge (connectors at the left and at the right side) 1x RP-SMA socket for connecting an external WLAN/BT antenna (2.4 / 5 GHz), not available on Article No. 100376 and 100378
Connectors	1 x 4-pole screw-type terminal for RS485 1 x 4-pole screw-type terminal for relay contact and signal input 1 x 4-pole screw-type terminal for power supply
Processor	Broadcom BCM2711, quad-core Arm Cortex-A72
Clock rate	1.5 GHz
Processor cooling	Passive with heat sink

Errors and omissions excepted.

KUNBUS GmbH, Heerweg 15C, 73770 Denkendorf, Germany | Tel: +49 (0) 711 400 91 500 | Fax: +49 (0) 711 400 91 501 |
Email: info@kunbus.com | Web: www.revolutionpi.com

V 1.1
1/2

REVOLUTION PI

RevPi Connect 4

RAM	2 GB LPDDR4 (Article No.: 100376, 100377), 4 GB LPDDR4 (Article No.: 100378, 100379), 8 GB LPDDR4 (Article No.: 100380)
Flash memory	8 GB (Article No.: 100376, 100377), 32 GB (Article No.: 100378, 100379, 100380)
WLAN / Bluetooth	2.4 GHz, 5.0 GHz IEEE 802.11 b/g/n/ac wireless; Bluetooth 5.0, BLE
Number of digital input channels	1
Digital input type	24 V DC control voltage (e.g. for power-good signal of a UPS)
Input thresholds	approx. 10 V DC (0 -> 1) resp. 7 V DC (1 -> 0); input current 2.4 mA (according to IEC 61131-2)
Number of digital output channels	1
Output type	opto-decoupled solid state relay, normally open, max. 30 V, 300 mA DC, any polarity
Software interface of input and output	Via GPIOs and process image.
Hardware watchdog	Watchdog in RTC device, freely configurable watchdog character device
Compatible modules for system expansion	All RevPi IO modules can be connected via the PiBridge system bus. Up to 5 modules can be connected as well to the left as to the right side of the device.
EMC interference emission	according to IEC 61000-6-4 Emission standard for industrial environments
EMC immunity	according to IEC 61000-6-2 Immunity standard for industrial environments
RTC buffer	CR2032 lithium battery, lifetime approx. 10 years
Optical indicator	6 status LEDs; 5 x red/green/blue, freely programmable, 1 x red/green
Conformity	CE, UKCA

¹ The bridging time required by EN 61131-2 of voltage dips of at least 10 ms and the max. USB output current are only guaranteed with a supply voltage 24 V -15 % / +20 %.

² The average power consumption without USB load varies greatly and depends on the use of the interfaces, the GPU and the CPU. It is usually well below 4 watts without HDMI.