

Item no.: 2898735

Data Sheet

Cable specification		
STYLE	H07RN-F 3G2.5	
Standard	EN50525	
Applications	Heavy outdoor wire	
Construction Details:		
Test Item	Unit	3G2.5
Conductor	Material	Copper
	Construction	49/0.238±0.005
	Conductor DC resistance at 20°C ≤	20°C ≤ 7.98Ω/km
Core Insulation	Material	EPDM
	Avg. thickness	mm 0.9
	Min. thickness	mm 0.71
	Over Diameter	mm 3.85±0.10
	Surface	Smooth
	Colors	yellow/green, brown, blue
lay	filler	NO
Jacket	Material	CPE
	Avg. thickness	mm 1.8
	Min. thickness	mm 1.43
	Over Diameter	mm 11.9±0.40
	Surface	Smooth
	Colors	BLACK
Marking	◁VDE▷ 40015999 H07RN-F 450/750V 3G2.5mm ² RIFENG	

