

Item no.: 2903454 – Black  
2903455 – Silver

## Data Sheet

---

Turning knob aluminium ( $\varnothing$  x H): 30 mm x 17 mm  
Inner bore dia.: 6.0 mm



### Technical data

Turning knob size ( $\varnothing$  x H): 30 mm x 17 mm

Inner bore diameter: 6 mm

Material: Aluminum

Operating & Storage temperature: -25 °C ~ +85 °C

Operating & Storage humidity: 20 %RH ~ 85 %RH

### Drawing:

