

Item no.: 2903480 – Silver  
2903471 – Black

## Data Sheet

---

Turning knob aluminium ( $\varnothing$  x H): 10 mm x 11 mm  
Inner bore dia.: 6.0 mm



### Technical data

Turning knob size ( $\varnothing$  x H): 10 mm x 11 mm

Inner bore diameter: 6 mm

Material: Aluminum & plastic

Operating & Storage temperature: -25 °C ~ +85 °C

Operating & Storage humidity: 20 %RH ~ 85 %RH

### Drawing:

