



Part Number : [1301470093](#)

Product Description : Watertite Extreme Connector with Locking Blade, 2 Pole/3 Wire, NEMA L5-30, 125V, Cord Grip Body Size F4

Series Number : 130147

Status : Active

Product Category : Wiring Devices

Engineering Number : 29W47



Documents & Resources

Drawings

[Drawing 1301470093_sd.pdf](#)

3D Models and Design Files

[3D Model 1301470093_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Not Reviewed per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Wiring Devices
Series	130147
Description	Watertite Extreme Connector with Locking Blade, 2 Pole/3 Wire, NEMA L5-30, 125V, Cord Grip Body Size F4
IP Rating	IP67
NEMA Configuration	NEMA L5-30
Product Family	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Specialty	N/A
Type	Connector
UPC	78678871331

Agency

CSA	LR6837
UL	E10176

Electrical

Current - Maximum per Contact	30.0A
GFCI	No
Voltage - Maximum	125V

Physical

Cord Grip Body Size	F4 1"
Cord Type	N/A
Flange	No
Flip Lid	No

Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	Yes
Poles	2-pole/3-wire
Receptacle Type	Single

This document was generated on Sep 26, 2023