



Part Number : [1301490011](#)

Product Description : Safeway Flanged Receptacle, 2 Pole/3 Wire, NEMA 5-20, 125V

Series Number : 130149

Status : Active

Product Category : Wiring Devices

Engineering Number : 1533MB



---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Wiring Devices

Series	130149
Description	Safeway Flanged Receptacle, 2 Pole/3 Wire, NEMA 5-20, 125V
IP Rating	N/A
NEMA Configuration	NEMA 5-20
Product Family	Heavy-Duty Industrial Wiring Devices
Product Name	Safeway
Specialty	N/A
Type	Receptacle
UPC	78678870311

### Agency

UL	E46237
----	--------

### Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	125V

### Physical

Cord Type	N/A
Flange	Yes
Flip Lid	No
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	No
Poles	2-pole/3-wire
Receptacle Type	Single