



Part Number : [355240920](#)

Product Description : VersaBlade Multi-Module 2-3-4 Hybrid Receptacle Housing, with Mounting Ears, 9 Circuits, Natural

Series Number : 35524

Status : Active

Product Category : Connector Housings



Documents & Resources

Drawings

[Drawing 355240920_sd.pdf](#)

3D Models and Design Files

[3D Model 355240920_stp.zip](#)

Specifications


[Application Specification 351500000AS_ENG-000.pdf](#)

[Packaging Specification PK-35524-001-001.pdf](#)

[Product Specification PS-35524-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	35524
Description	VersaBlade Multi-Module 2-3-4 Hybrid Receptacle Housing, with Mounting Ears, 9 Circuits, Natural
Application	Power, Wire-to-Wire
Product Family	VersaBlade Wire-to-Wire Connector System
Product Name	VersaBlade
UPC	800754835329

Agency

UL	E29179
----	--------

Physical

Breakaway	No
Circuits (maximum)	9
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	11.501/g
Number of Rows	3
Packaging Type	Bag

Panel Mount	Yes
Pitch - Mating Interface	6.20mm, 7.30mm
Pitch - Termination Interface	6.20mm, 7.30mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +120°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
VersaBlade Hybrid Plug Housing, 2 Circuits, Positive Lock, Natural	<u>0351510210</u>
VersaBlade Hybrid Plug Housing, 2 Circuits, Positive Lock, Blue	<u>0351510214</u>
VersaBlade Hybrid Plug Housing, 2 Circuits, Positive Lock, Natural, Glow-Wire Capable	<u>0351510219</u>
VersaBlade Hybrid Plug Housing, 2 Circuits, Positive Lock, Red, Glow-Wire Capable	<u>0351512219</u>
VersaBlade Hybrid Plug Housing, 2 Circuits, Positive Lock, Yellow, Glow-Wire Capable	<u>0351513219</u>
VersaBlade Hybrid Plug Housing, 2 Circuits, Positive Lock, Blue, Glow-Wire Capable	<u>0351514219</u>
VersaBlade Hybrid Plug Housing, 3 Circuits, Positive Lock, Natural	<u>0351510310</u>
VersaBlade Hybrid Plug Housing, 3 Circuits, Positive Lock, Blue	<u>0351510314</u>
VersaBlade Hybrid Plug Housing, 3 Circuits, Positive Lock, Natural, Glow-Wire Capable	<u>0351510319</u>
VersaBlade Hybrid Plug Housing, 3 Circuits, Positive Lock, Blue, Glow-Wire Capable	<u>0351514319</u>
VersaBlade Hybrid Plug Housing, 4 Circuits, Positive Lock, Natural	<u>0351510410</u>
VersaBlade Hybrid Plug Housing, 4 Circuits, Positive Lock, Blue	<u>0351510414</u>
VersaBlade Hybrid Plug Housing, 4 Circuits, Positive Lock, Natural, Glow-Wire Capable	<u>0351510419</u>

VersaBlade Hybrid Plug Housing, 4 Circuits, Positive Lock, Blue, Glow-Wire Capable	<u>0351514419</u>
------------------------------------------------------------------------------------	-------------------

Use with Part(s)

Description	Part Number
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Natural	/content/molex/molex-dot-com/us/en/products/product-page.html/351500290.html
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Red	/content/molex/molex-dot-com/us/en/products/product-page.html/351500292.html
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Yellow	/content/molex/molex-dot-com/us/en/products/product-page.html/351500293.html
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Blue	/content/molex/molex-dot-com/us/en/products/product-page.html/351500294.html
VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Natural	/content/molex/molex-dot-com/us/en/products/product-page.html/351500390.html
VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Red	/content/molex/molex-dot-com/us/en/products/product-page.html/351500392.html
VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Yellow	/content/molex/molex-dot-com/us/en/products/product-page.html/351500393.html
VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Blue	/content/molex/molex-dot-com/us/en/products/product-page.html/351500394.html
VersaBlade Male Crimp Terminals	<u>35745</u>
VersaBlade Female Crimp Terminals	<u>35746</u>
VersaBlade Male Crimp Terminals	<u>35747</u>