



**Part Number :** [26607021](#)  
**Product Description :** KK 396 Solid Right-Angle Header, Friction Lock, with Snap-in Plastic Peg PCB Lock, 2 Circuits, Gold (Au) Plating  
**Series Number :** 42892  
**Status :** Active  
**Product Category :** PCB Headers and Receptacles  
**Engineering Number :** 42892-0019



Documents & Resources

**Drawings**  
[Drawing 026607021\\_sd.pdf](#)  
[Packaging Design Drawing PK-42492-002-001.pdf](#)

**3D Models and Design Files**  
[3D Model 026607021\\_stp.zip](#)

**Specifications**  
[Product Specification PS-08-50-001.pdf](#)

Product Environment Compliance

Compliance

|                    |                                                |
|--------------------|------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                   |
| China RoHS         |                                                |
| EU ELV             | Not Relevant                                   |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21             |
| REACH SVHC         | Not Contained per D(2023)3788-DC (14 Jun 2023) |
| EU RoHS            | Compliant per EU 2015/863                      |

Multiple Part Product Compliance Statements  
- Eu RoHS  
- REACH SVHC  
- Low-Halogen

## Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

|                |                                                                                                                  |
|----------------|------------------------------------------------------------------------------------------------------------------|
| Status         | Active                                                                                                           |
| Category       | PCB Headers and Receptacles                                                                                      |
| Series         | 42892                                                                                                            |
| Description    | KK 396 Solid Right-Angle Header, Friction Lock, with Snap-in Plastic Peg PCB Lock, 2 Circuits, Gold (Au) Plating |
| Application    | Power, Wire-to-Board                                                                                             |
| Component Type | PCB Header                                                                                                       |
| Product Family | KK Interconnect Systems                                                                                          |
| Product Name   | KK 396                                                                                                           |
| UPC            | 800754921046                                                                                                     |

#### Agency

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

#### Electrical

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 7.0A |
| Voltage - Maximum             | 250V |

#### Physical

|                                |       |
|--------------------------------|-------|
| Breakaway                      | No    |
| Circuits (Loaded)              | 2     |
| Circuits (maximum)             | 2     |
| Durability (mating cycles max) | 100   |
| Flammability                   | 94V-0 |

|                                |                           |
|--------------------------------|---------------------------|
| Glow-Wire Capable              | No                        |
| Lock to Mating Part            | Yes                       |
| Material - Metal               | Brass                     |
| Material - Plating Mating      | Gold                      |
| Material - Plating Termination | Matte Tin                 |
| Net Weight                     | 0.888/g                   |
| Number of Rows                 | 1                         |
| Orientation                    | Right Angle               |
| Packaging Type                 | Bag                       |
| PC Tail Length                 | 3.30mm                    |
| PCB Locator                    | Yes                       |
| PCB Retention                  | Yes                       |
| PCB Thickness - Recommended    | 1.60mm                    |
| Pitch - Mating Interface       | 3.96mm                    |
| Plating min - Mating           | 0.508µm                   |
| Plating min - Termination      | 0.508µm                   |
| Polarized to Mating Part       | Yes                       |
| Polarized to PCB               | Yes                       |
| Shrouded                       | Partial                   |
| Stackable                      | Yes                       |
| Temperature Range - Operating  | See Product Specification |
| Termination Interface Style    | Through Hole              |

## Solder Process Data

|                              |      |
|------------------------------|------|
| Max-Duration                 | 5    |
| Lead-Free Process Capability | WAVE |
| Max-Cycle                    | 1    |
| Max-Temp                     | 235  |

---

## Mates With / Use With

### Mates with Part(s)

| Description                         | Part Number |
|-------------------------------------|-------------|
| KK 3.96mm Single Row Crimp Housings | <u>2139</u> |

|                                           |              |
|-------------------------------------------|--------------|
| KK 3.96mm Single Row Crimp Housings       | <u>3069</u>  |
| KK 3.96mm Crimp Housings                  | <u>41695</u> |
| KK 396 PC Board Connector                 | <u>41815</u> |
| KK 3.96mm Pitch Single Row Crimp Housings | <u>6442</u>  |

---

This document was generated on Sep 26, 2023