



**Part Number :** [190010001](#)  
**Product Description :** Avikrimp Quick Disconnect, Male, for 18-22 (0.80-0.35mm<sup>2</sup>), Box, Tab 6.35 x 0.81mm  
**Series Number :** 19001  
**Status :** Active  
**Product Category :** Quick Disconnects  
**Engineering Number :** AA-5260



## Documents & Resources

### Drawings

[Drawing 190010001\\_sd.pdf](#)

### 3D Models and Design Files

[3D Model 190010001\\_stp.zip](#)

### Specifications

[Product Specification PS-19902-011-001.pdf](#)

[Product Specification PS-19902-013-001.pdf](#)

[Product Specification PS-19902-014-001.pdf](#)

## Product Environment Compliance

### Compliance

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                          |
| China RoHS         |  |
| EU ELV             | Not Relevant                                                                          |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21                                                        |
| REACH SVHC         | Not Contained per D(2023)3788-DC (14 Jun 2023)                                        |
| EU RoHS            | Compliant per EU 2015/863                                                             |

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC

- Low-Halogen

#### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### EU RoHS Certificate of Compliance

---

### Part Details

#### General

|                |                                                                                                |
|----------------|------------------------------------------------------------------------------------------------|
| Status         | Active                                                                                         |
| Category       | Quick Disconnects                                                                              |
| Series         | 19001                                                                                          |
| Description    | Avikrimp Quick Disconnect, Male, for 18-22 (0.80-0.35mm <sup>2</sup> ), Box, Tab 6.35 x 0.81mm |
| Product Family | Standard Quick-Disconnect Terminals                                                            |
| Product Name   | Avikrimp                                                                                       |
| Type           | Quick Disconnect                                                                               |
| UPC            | 800753026513                                                                                   |

#### Agency

|     |         |
|-----|---------|
| CSA | LR18689 |
| UL  | E79133  |

#### Electrical

|                   |      |
|-------------------|------|
| Voltage - Maximum | 300V |
|-------------------|------|

#### Physical

|                   |        |
|-------------------|--------|
| Barrel Type       | Closed |
| Color - Resin     | Red    |
| Flammability      | 94V-2  |
| Gender            | Male   |
| Glow-Wire Capable | No     |

|                                |                |
|--------------------------------|----------------|
| Insulated                      | Fully          |
| Insulation                     | Nylon (PA)     |
| Lock to Mating Part            | None           |
| Material - Metal               | Brass          |
| Material - Plating Mating      | Zinc Chromate  |
| Material - Plating Termination | Zinc Chromate  |
| Net Weight                     | 1.486/g        |
| Orientation                    | Straight       |
| Packaging Type                 | Bag            |
| Plating min - Mating           | 5.080µm        |
| Plating min - Termination      | 5.080µm        |
| Polarized to Mating Part       | No             |
| Tab Thickness                  | 0.81mm         |
| Tab Width                      | 6.35mm         |
| Temperature Range - Operating  | -65° to +105°C |
| Wire Insulation Diameter       | 3.56mm max.    |
| Wire Size (AWG)                | 18, 20, 22     |

## Solder Process Data

|                              |     |
|------------------------------|-----|
| Lead-Free Process Capability | N/A |
|------------------------------|-----|

## Use with Part(s)

| Description                                                                        | Part Number                                                                                                                                                             |
|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Avikrimp Fully Insulated Quick Disconnect, Female for 18-22 AWG Wire, Box          | <a href="/content/molex/molex-dot-com/us/en/products/product-page.html/190020001.html">/content/molex/molex-dot-com/us/en/products/product-page.html/190020001.html</a> |
| Avikrimp Fully Insulated Quick Disconnect, Female, for 18-22 AWG Wire, Mylar Tape  | <a href="/content/molex/molex-dot-com/us/en/products/product-page.html/190020002.html">/content/molex/molex-dot-com/us/en/products/product-page.html/190020002.html</a> |
| Avikrimp Fully Insulated Quick Disconnect, Female, for 18-22 AWG Wire, Metal Strip | <a href="/content/molex/molex-dot-com/us/en/products/product-page.html/190020004.html">/content/molex/molex-dot-com/us/en/products/product-page.html/190020004.html</a> |

## Application Tooling

### Global

| Description | Part Number |
|-------------|-------------|
|-------------|-------------|

|                                                  |                   |
|--------------------------------------------------|-------------------|
| Hand Crimp Tool                                  | <u>0640012600</u> |
| Crimp Head for the AT-200<br>Pneumatic Hand Tool | <u>0640052600</u> |