



Part Number : [190020027](#)

Product Description : Avikrimp Fully Insulated Quick Disconnect, Female, for 14-16 AWG Wire, Metal Strip

Series Number : 19002

Status : Active

Product Category : Quick Disconnects

Engineering Number : BB-5263Z



---

## Documents & Resources

### Drawings

[Drawing 190020027\\_sd.pdf](#)

### 3D Models and Design Files

[3D Model 190020027\\_stp.zip](#)

### Specifications

[Product Specification PS-19902-011-001.pdf](#)

[Product Specification PS-19902-014-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

### [Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

## Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Quick Disconnects
Series	19002
Description	Avikrimp Fully Insulated Quick Disconnect, Female, for 14-16 AWG Wire, Metal Strip
Product Family	Standard Quick-Disconnect Terminals
Product Name	Avikrimp
Type	Quick Disconnect
UPC	800753027367

#### Agency

CSA	LR18689
UL	E79133

#### Electrical

Voltage - Maximum	300V
-------------------	------

#### Physical

Barrel Type	Closed
Color - Resin	Blue
Flammability	94V-2
Gender	Female
Glow-Wire Capable	No
Insulated	Fully
Insulation	Nylon (PA)

Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.158/g
Orientation	Straight
Packaging Type	Reel
Polarized to Mating Part	No
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	-40° to +105°C
Wire Insulation Diameter	3.94mm max.
Wire Size (AWG)	14, 16
Wire Size mm <sup>2</sup>	1.30-2.00

#### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

#### Use with Part(s)

Description	Part Number
Avikrimp Quick Disconnect, Male, for 14-16 (2.00-1.30mm <sup>2</sup> ), Box, Tab 6.35 x 0.81mm	<a href="/content/molex/molex-dot-com/us/en/products/product-page.html/190010006.html">/content/molex/molex-dot-com/us/en/products/product-page.html/190010006.html</a>
Avikrimp Quick Disconnect, Male, for 14-16 (2.00-1.30mm <sup>2</sup> ), Mylar Tape, Tab 6.35 x 0.81mm	<a href="/content/molex/molex-dot-com/us/en/products/product-page.html/190010007.html">/content/molex/molex-dot-com/us/en/products/product-page.html/190010007.html</a>

#### Application Tooling

##### Global

Description	Part Number
Mini-Mac Applicator	<a href="#">0638810200</a>