



Part Number : [190020044](#)
Product Description : Avikrimp Fully Insulated Quick Disconnect, Female, for 10-12 (5.00-3.30mm²) Wire, Box, Tab 6.35 x 0.81mm
Series Number : 19002
Status : Active
Product Category : Quick Disconnects
Engineering Number : C-5265



Documents & Resources

Drawings

[Drawing 190020044_sd.pdf](#)

3D Models and Design Files

[3D Model 190020044_stp.zip](#)

Specifications

- [Product Specification PS-19902-011-001.pdf](#)
- [Product Specification PS-19902-013-001.pdf](#)
- [Product Specification PS-19902-014-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19002
Description	Avikrimp Fully Insulated Quick Disconnect, Female, for 10-12 (5.00-3.30mm ²) Wire, Box, Tab 6.35 x 0.81mm
Product Family	Standard Quick-Disconnect Terminals
Product Name	Avikrimp
Type	Quick Disconnect
UPC	800753027763

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	300V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Yellow
Flammability	94V-2
Gender	Female
Glow-Wire Capable	No

Insulated	Fully
Insulation	Nylon (PA)
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.941/g
Orientation	Straight
Packaging Type	Bag
Polarized to Mating Part	No
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	-65° to +105°C
Wire Insulation Diameter	6.22mm max.
Wire Size (AWG)	10, 12

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Use with Part(s)

Description	Part Number
Avikrimp Quick Disconnect, Male, for 10-12 (5.00-3.30mm ²), Box, Tab 6.35 x 0.81mm	/content/molex/molex-dot-com/us/en/products/product-page.html/190010010.html
Avikrimp Quick Disconnect, Male, for 10-12 (5.00-3.30mm ²), Mylar Tape, Tab 6.35 x 0.81mm	/content/molex/molex-dot-com/us/en/products/product-page.html/190010011.html

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Insulkrimp Quick Disconnect Terminals, 10-22 AWG	0640010200
ServiceGrade Hand Crimp Tool - Ratchet	0640160037

