



Part Number : [190380013](#)
Product Description : InsulKrimp Snap
Receptacle, for 14-16 AWG Wire, Nylon, Fits
Male Plug Diameter 4.57mm
Series Number : 19038
Status : Active
Product Category : Quick Disconnects
Engineering Number : BRB-2180N



Documents & Resources

Drawings

[Drawing 190380013_sd.pdf](#)

3D Models and Design Files

[3D Model 190380013_stp.zip](#)

Specifications

[Product Specification PS-19902-011-001.pdf](#)

[Product Specification PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19038
Description	InsulKrimp Snap Receptacle, for 14-16 AWG Wire, Nylon, Fits Male Plug Diameter 4.57mm
Comments	Fits Male Plug Dia. 4.57mm
Product Family	Snap Plugs and Receptacles
Product Name	InsulKrimp
Type	Snap Receptacle
UPC	800753048812

Agency

CSA	LR18689
UL	E152602

Electrical

Voltage - Maximum	600V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Blue
Flammability	94V-2
Gender	Female
Glow-Wire Capable	No
Insulated	Fully

Insulation	Nylon (PA)
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1.161/g
Orientation	Straight
Packaging Type	Bag
Tab Thickness	N/A
Tab Width	N/A
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.81mm max.
Wire Size (AWG)	14, 16
Wire Size mm ²	1.00-2.50

Application Tooling

Global

Description	Part Number
Hand Crimp Tool	<u>0640012100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>0640052100</u>