



Part Number : [190390001](#)


Product Description : Avikrimp Snap Receptacle, for 18-22 AWG Wire, PVC, Fits Male Plug Diameter 3.96mm

Series Number : 19039

Status : Active

Product Category : Quick Disconnects

Engineering Number : BRA-8156



Documents & Resources

Drawings

[Drawing 190390001_sd.pdf](#)

3D Models and Design Files

[3D Model 190390001_stp.zip](#)


Specifications

[Product Specification PS-19902-011-001.pdf](#)

[Product Specification PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead monoxide per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS

- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19039
Description	Avikrimp Snap Receptacle, for 18-22 AWG Wire, PVC, Fits Male Plug Diameter 3.96mm
Comments	Fits Male Plug Dia. 3.96mm
Product Family	Snap Plugs and Receptacles
Product Name	Avikrimp
Type	Snap Receptacle
UPC	800753049307

Agency

CSA	LR18689
UL	E152602

Electrical

Voltage - Maximum	Per Wire Specification
-------------------	------------------------

Physical

Barrel Type	Closed
Color - Resin	Red
Flammability	94V-0
Gender	Female
Glow-Wire Capable	No

Insulated	Fully
Insulation	PVC
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	PVC
Net Weight	1.241/g
Orientation	Straight
Packaging Type	Bag
Plating min - Mating	4.064µm
Plating min - Termination	4.064µm
Tab Thickness	N/A
Tab Width	N/A
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.25mm max.
Wire Size (AWG)	18, 20, 22

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Hand Crimp Tool	<u>0640012300</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>0640052300</u>