




Part Number : [190690040](#)
Product Description : Krimptite Ring Tongue
Terminal for 18-22 AWG Wire
Series Number : 19069
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : AA-122-10



Documents & Resources

Drawings

[Drawing 190690040_sd.pdf](#)

3D Models and Design Files

[3D Model 190690040_stp.zip](#)

Specifications

[Product Specification PS-19902-011-001.pdf](#)

[Product Specification PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19069
Description	Krimptite Ring Tongue Terminal for 18-22 AWG Wire
Keyword	Ring Terminal, Ring Terminals
Product Family	Solderless Terminals
Product Name	Krimptite
Type	Ring
UPC	800755066340

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.897/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	10 (M5)
Termination Interface Style	Crimp or Compression

Wire Size (AWG)	18, 20, 22
Wire Size mm ²	0.35-0.80

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm ² - 0.5mm ²	<u>0640030100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>0640070100</u>
ServiceGrade Hand Crimp Tool - Ratchet	<u>0640160038</u>