



Part Number : [191410052](#)
Product Description : Krimptite Spade Tongue
Terminal for 14-16 AWG Wire
Series Number : 19141
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : BB-107-06



Documents & Resources

Drawings

[Drawing 191410052_sd.pdf](#)

Specifications

[Product Specification PS-19902-011-001.pdf](#)

[Product Specification PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19141
Description	Krimptite Spade Tongue Terminal for 14-16 AWG Wire
Keyword	Spade Terminal, Spade Terminals
Product Family	Solderless Terminals
Product Name	Krimptite
Type	Spade
UPC	800755086461

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.520/g
Packaging Type	Bag
Stud Size	5-6 (M3-3.5)
Termination Interface Style	Crimp or Compression
Wire Size (AWG)	14, 16
Wire Size mm ²	1.30-2.00

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

This document was generated on Sep 26, 2023