



Part Number : [191640075](#)
Product Description : Perma-Seal Male Quick Disconnect Tab for 10-12 AWG Wire, Tab Size 6.35 x 0.81mm, Bag
Series Number : 19164
Status : Active
Product Category : Quick Disconnects
Engineering Number : SC-9280



Documents & Resources

Drawings

[Drawing 191640075_sd.pdf](#)

Specifications

[Product Specification PS-19902-013-001.pdf](#)

[Product Specification PS-19902-011-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19164
Description	Perma-Seal Male Quick Disconnect Tab for 10-12 AWG Wire, Tab Size 6.35 x 0.81mm, Bag
Product Family	Perma-Seal Terminals
Product Name	Perma-Seal
Type	Quick Disconnect
UPC	800753113596

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	600V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Yellow
Gender	Male
Glow-Wire Capable	No
Insulated	Fully
Insulation	NiAc
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Zinc Chromate

Material - Plating Termination	Zinc Chromate
Material - Resin	Nylon
Net Weight	2.830/g
Orientation	Straight
Packaging Type	Bag
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	-55° to +125°C
Wire Insulation Diameter	5.84mm max.
Wire Size (AWG)	10, 12
Wire Size mm ²	4.00-6.00

Application Tooling

Global

Description	Part Number
Hand Crimp Tool	<u>0640016100</u>

This document was generated on Sep 26, 2023