




Part Number : 191890008
Product Description : Krimptite Butt Splice for
14-16 AWG Wire
Series Number : 19189
Status : Active
Product Category : Splices
Engineering Number : B-131



Documents & Resources

Drawings
Drawing 191890008_sd.pdf

Specifications
Product Specification PS-19902-011-001.pdf
Product Specification PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Splices
Series	19189
Description	Krimptite Butt Splice for 14-16 AWG Wire
Product Family	Splices
Product Name	Butt,Krimptite
UPC	800755048803

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.943/g
Packaging Type	Bag
Wire Size (AWG)	14, 16

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm ² - 0.5mm ²	<u>0640030100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>0640070100</u>
ServiceGrade Hand Crimp Tool - Ratchet	<u>0640160038</u>

This document was generated on Sep 26, 2023