




Part Number : [191930281](#)
Product Description : VersaKrimp Ring
Tongue Terminal for 4 AWG Wire
Series Number : 19193
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : F-369-12



Documents & Resources

Drawings
[Drawing 191930281_sd.pdf](#)

Specifications
[Product Specification PS-19902-011-001.pdf](#)
[Product Specification PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)
- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)
- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19193
Description	VersaKrimp Ring Tongue Terminal for 4 AWG Wire
Keyword	Ring Terminal, Ring Terminals
Product Family	VersaKrimp Terminals and Splices
Product Name	VersaKrimp
Type	Ring
UPC	800755051131

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	13.218/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	1/2" (M12)
Termination Interface Style	Crimp or Compression
Wire Size (AWG)	4

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Manual Putt Pump Hydraulic System, Die set required	<u>0192860117</u>
Die Set (Large) for the HHLS Hydraulic Crimper	<u>0192900007</u>
Hydraulic Dieless Crimping Tool	<u>0638161700</u>
Square "DIN" Style Dies for 4 AWG	<u>0640037870</u>