




Part Number : [191930342](#)
Product Description : VersaKrimp Ring
Tongue Terminal for 2/0 AWG Wire
Series Number : 19193
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : J-385-14



Documents & Resources

Drawings
[Drawing 191930342_sd.pdf](#)

Specifications
[Product Specification PS-19902-011-001.pdf](#)
[Product Specification PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not saleable
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)
- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)
- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19193
Description	VersaKrimp Ring Tongue Terminal for 2/0 AWG Wire
Keyword	Ring Terminal, Ring Terminals
Product Family	VersaKrimp Terminals and Splices
Product Name	VersaKrimp
Type	Ring
UPC	800755052251

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	28.087/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	1/4" (M6)
Termination Interface Style	Crimp or Compression
Wire Size (AWG)	2/0

Application Tooling

Global

Description	Part Number
Manual Putt Pump Hydraulic System, Die set required	<u>0192860117</u>
Die Set (Large) for the HHLS Hydraulic Crimper	<u>0192900012</u>
Manual tool for Crimping non-insulated 8AWG thru 4/0 Terminals	<u>0192940008</u>
Hydraulic Dieless Crimping Tool	<u>0638161700</u>
Square "Din" Style Die Set for BCL and VersaKrimp Un-insulated Ring Tongue Terminals and Splices, 1/0 and 2/0 AWG	<u>0640038070</u>

This document was generated on Sep 26, 2023