



Part Number : [191980004](#)
Product Description : Avikrimp Spade Tongue
Terminal for 18-22 AWG Wire
Series Number : 19198
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : AA-835-08



Documents & Resources

Drawings

[Drawing 191980004_sd.pdf](#)

Specifications

[Product Specification PS-19902-013-001.pdf](#)

[Product Specification PS-19902-011-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19198
Description	Avikrimp Spade Tongue Terminal for 18-22 AWG Wire
Keyword	Spade Terminal, Spade Terminals
Product Family	Solderless Terminals
Product Name	Avikrimp
Type	Spade
UPC	800753045958

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Flammability	94V-0
Insulation	Nylon (PA)
Material - Plating Mating	Tin
Net Weight	0.816/g
Packaging Type	Bag
Stud Size	8 (M4)
Wire Insulation Diameter	3.60mm max.
Wire Size (AWG)	18, 20, 22
Wire Size mm ²	0.35-0.80

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 10-22 AWG and 6.0-0.5mm ² (Rings, Spades, Hooks, Block Spades and Flanged Spades)	<u>0640010100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>0640050100</u>
ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool	<u>0640160036</u>

This document was generated on Sep 26, 2023