



Part Number : [192030085](#)
Product Description : Krimptite Temp-Term
Ring Tongue Terminal for 14 to 16 AWG Wire,
Stud Size 10 (M5)
Series Number : 19203
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : BB-U-137-10



Documents & Resources

Drawings
[Drawing 192030085_sd.pdf](#)

Specifications
[Product Specification PS-19902-011-001.pdf](#)
[Product Specification PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents
- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19203
Description	Krimptite Temp-Term Ring Tongue Terminal for 14 to 16 AWG Wire, Stud Size 10 (M5)
Comments	1200° F (649° C)
Keyword	Ring Terminal, Ring Terminals
Product Family	High-Temperature Temp Terms Terminals and Splices
Product Name	Krimptite,Temp-Terms
Type	Ring
UPC	800755059427

Agency

UL	E32244
----	--------

Physical

Barrel Type	Closed
Insulation	None
Net Weight	0.592/g
Packaging Type	Bag
Stud Size	10 (M5)
Wire Size (AWG)	14, 16
Wire Size mm ²	1.00-2.50

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm ² - 0.5mm ²	<u>0640030100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>0640070100</u>
ServiceGrade Hand Crimp Tool - Ratchet	<u>0640160038</u>

This document was generated on Sep 26, 2023