



Part Number : [192760005](#)
Product Description : Quixon Quick Disconnect, InsulKrimp Style, Female, Fully Insulated Blue, 14-16 AWG, Loose
Series Number : 19276
Status : Active
Product Category : Quick Disconnects
Engineering Number : BB-2206-LIF



Documents & Resources

Drawings

[Drawing 192760005_sd.pdf](#)

3D Models and Design Files

[3D Model 192760005_stp.zip](#)

Specifications

[Product Specification PS-19902-011-001.pdf](#)

[Product Specification PS-19902-012-001.pdf](#)

[Product Specification PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19276
Description	Quixon Quick Disconnect, InsulKrimp Style, Female, Fully Insulated Blue, 14-16 AWG, Loose
Comments	Low Insertion Force
Product Family	Quixon Terminals
Product Name	InsulKrimp,Quixon
Type	Quick Disconnect
UPC	884982565111

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	600V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Blue
Flammability	94V-2
Gender	Female
Glow-Wire Capable	No

Insulated	Fully
Insulation	Nylon (PA)
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.943/g
Orientation	Straight
Packaging Type	Bag
Tab Thickness	0.41mm
Tab Width	7.87mm
Temperature Range - Operating	-55° to +105°C
Wire Insulation Diameter	4.06mm
Wire Size (AWG)	14, 16

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Insulkrimp Quick Disconnect Terminals, 10-22 AWG	<u>0640010400</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>0640050400</u>