



Part Number : [193230008](#)
Product Description : VersaKrimp Metric Ring
Terminal for M4 Stud Size (#8), Un-insulated,
Bag
Series Number : 19323
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : BB2,5-337-M4



Documents & Resources

- Drawings**
[Drawing 193230008_sd.pdf](#)
- 3D Models and Design Files**
[3D Model 193230008_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

- Multiple Part Product Compliance Statements
- Eu RoHS
 - REACH SVHC
 - Low-Halogen
- Multiple Part Industry Compliance Documents
- IPC 1752A Class C
 - IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19323
Description	VersaKrimp Metric Ring Terminal for M4 Stud Size (#8), Un-insulated, Bag
Keyword	Ring Terminal, Ring Terminals
Product Family	Metric Ring Terminals
Product Name	VersaKrimp
Type	Ring
UPC	887191289922

Agency

UL	E32244
----	--------

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Net Weight	0.669/g
Packaging Type	Bag
Stud Size	M4
Wire Size (AWG)	N/A
Wire Size mm ²	1.00-2.50

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm ² - 0.5mm ²	<u>0640030100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>0640070100</u>
ServiceGrade Hand Crimp Tool - Ratchet	<u>0640160038</u>

This document was generated on Sep 26, 2023