




Part Number : [464379308](#)
Product Description : EXTreme Ten60Power
Right-Angle Plug with Side Guides, 8 DC Power
Circuits, Press Fit Tail
Series Number : 46437
Status : Active
Product Category : Board-to-Board
Connectors



Documents & Resources

Drawings
[Drawing 464379308_sd.pdf](#)
[Packaging Design Drawing 464371001-PK-000.pdf](#)

3D Models and Design Files
[3D Model 464379308_stp.zip](#)

Specifications
[Product Specification PS-46436-100-001.pdf](#)
[Test Summary 464361000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)
- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	46437
Description	EXTreme Ten60Power Right-Angle Plug with Side Guides, 8 DC Power Circuits, Press Fit Tail
Application	Board-to-Board, Power
Comments	See Product Specification for details
Component Type	PCB Header
Product Family	EXTreme Ten60 High-Power Connectors
Product Name	EXTreme Ten60Power
UPC	195842664852

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	60.0A
Voltage - Maximum	600V AC / 250V DC

Physical

Breakaway	No
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black
Durability (mating cycles max)	200

First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Side, Yes
Keying to Mating Part	None
Lock to Mating Part	No
Mated Height	10.00mm
Material - Metal	High Conductivity Copper
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	24.391/g
Number of Rows	1
Orientation	Right Angle
Packaging Type	Tray
PC Tail Length	3.28mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.58mm
Pitch - Mating Interface	5.50mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
(p)ower-(s)ignal Configuration	8p - 0s
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole - Compliant Pin

Mates With / Use With

Mates with Part(s)

Description	Part Number
EXTreme Ten60Power Right-Angle Receptacle with Side Guides, 8 DC Power Circuits, Press Fit Tail	<u>0464369308</u>

EXTreme Ten60Power Vertical Receptacle with Side Guides, 8 DC Power Circuits, Press Fit Tail	<u>0465629308</u>
--	-------------------