



Part Number : [734035111](#)
Product Description : 50 Ohms, FAKRA SMB Jack, Right-Angle, Through Hole, Brass Body, Keying Option B, Natural
Series Number : 73403
Status : Active
Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings

[Drawing 734035111_sd.pdf](#)

3D Models and Design Files

[3D Model 734035111_stp.zip](#)

Specifications

[Product Specification PS-89675-331-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73403
Description	50 Ohms, FAKRA SMB Jack, Right-Angle, Through Hole, Brass Body, Keying Option B, Natural
Application	Automotive
Product Family	FAKRA PCB, Cable and Sealed Connection Systems
Product Name	FAKRA,SMB
Style	PCB
Type	Subminiature
UPC	883906687625

Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 335 Vrms@Sea Level

Physical

Gender	Jack
Keying to Mating Part	Yes
Net Weight	4.441/g
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Through Hole
Reverse Polar	No
Wire/Cable Type	N/A

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	SMC&WAVE
Max-Cycle	2
Max-Temp	260