



Part Number : [885366203](#)

Product Description : MPO QSFP-to-MPO QSFP Fiber Optic Jumper Cable Assembly, High Bandwidth (OM3), Multimode, 12 Fiber Round Plenum Cable, 3.0m Length

Series Number : 106283

Status : Active

Product Category : Fiber Optic Cable Assemblies



---

## Documents & Resources

### Drawings

[Drawing 885366203\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Fiber Optic Cable Assemblies
Series	106283
Description	MPO QSFP-to-MPO QSFP Fiber Optic Jumper Cable Assembly, High Bandwidth (OM3), Multimode, 12 Fiber Round Plenum Cable, 3.0m Length
Connector to Connector	MPO-to-MPO
Mode	Multimode
Product Name	MPO,QSFP
UPC	195842246270

### Physical

Boot Type	Straight
Cable Length	3.0m
Cable Size	3.00mm
Fiber (Core/Cladding)	50/125µm OM3
Net Weight	46.000/g
Single Ended	No
Wire/Cable Type	12 Fiber Round, Plenum