



Part Number : [1200835015](#)
Product Description : Ultra-Lock (M12) Single-Ended Cordset, 12 Poles, Male (Straight) to Pigtail, 26 AWG, PUR Cable, 2.0m (6.56') Length, Black
Series Number : 120083
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Number : W0CS06P45M020



Documents & Resources

Drawings
[Drawing 1200835015_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120083
Description	Ultra-Lock (M12) Single-Ended Cordset, 12 Poles, Male (Straight) to Pigtail, 26 AWG, PUR Cable, 2.0m (6.56') Length, Black
IP Rating	IP67
Product Family	Brad Ultra-Lock Connection System
Product Name	Ultra-Lock (M12)
Region	America
Type	Single Ended
UPC	883906540784

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	30V AC/DC

Physical

Cable Diameter	6.50mm (.256")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Yellow
Connector End A	Ultra-Lock (M12)
Connector End B	Pigtail
Coupling Style	Push to Lock
Gender	Male-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer

Material - Plating Mating	Gold
Orientation	Straight to Pigtail
Poles	12
Temperature Range - Operating	-25° to +90°C
Wire/Cable Type	UL 20549
Wire Size (AWG)	26

Mates With / Use With

Mates with Part(s)

Description	Part Number
Micro-Change M12 CAT6A Cordsets and Receptacles	<u>120341</u>