



Part Number : [1200850016](#)
Product Description : Ultra-Lock (M12) Single Keyway with PG7 Cable Fitting, Female, 5 Pole, Right-Angle, Cable Diameter 3.30-6.60mm
Series Number : 120085
Status : Active
Product Category : Circular Industrial Connectors
Engineering Number : WA5001-31



Documents & Resources

Drawings
[Drawing 1200850016_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

ZZCERT_UKCA - Declaration of Conformity : CER_4000410300_00_000.pdf

ZZCERT_CE - Declaration of Conformity : CER_4000410038_00_000.pdf

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	120085
Description	Ultra-Lock (M12) Single Keyway with PG7 Cable Fitting, Female, 5 Pole, Right-Angle, Cable Diameter 3.30-6.60mm
Approvals	cCSAus certified
IP Rating	IP69K
Product Family	Brad Ultra-Lock Connection System
Product Name	Ultra-Lock (M12)
Type	Field Attachable Connector
UPC	78678897659

Agency

CSA	LR6837
-----	--------

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	30V AC / 36V DC

Physical

Cable Diameter	3.30-6.60mm (.130-.260")
Coupling Type	Push to Lock
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Female
Keyway	Single

Material - Connector Body	PA
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	1.000/g
Orientation	90° Angle
Poles	5
Temperature Range - Operating	-25°C to +90°C
Wire Size (AWG)	18

This document was generated on Sep 26, 2023