



Part Number : [1201010001](#)
Product Description : PROFIBUS Data Line
Mini-Change Tee, 5 Poles, Female/Male with
Female Drop
Series Number : 120101
Status : Active
Product Category : Industrial Tees and
Splitters
Engineering Number : PBAPT



Documents & Resources

Drawings
[Drawing 1201010001_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; Medium-chain chlorinated paraffins (MCCP) per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

ZZCERT_UKCA - Declaration of Conformity : CER_4000410285_00_000.pdf

ZZCERT_CE - Declaration of Conformity : CER_4000408918_00_000.pdf

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	120101
Description	PROFIBUS Data Line Mini-Change Tee, 5 Poles, Female/Male with Female Drop
IP Rating	IP67
Product Name	PROFIBUS Data Line
Type	Power Tap Tee
UPC	78678850377

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	600V AC/DC

Physical

Drop Connector	Mini-Change
Drop Gender	Female
Keyway	Single
LED Indicator	No
Left Trunk Connector	Mini-Change
Left Trunk Gender	Female
Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A

Material - Connector Body	TPE
Material - Coupling Nut	Black Epoxy Coated Zinc
Net Weight	176.670/g
Poles	5
Right Trunk Connector	Mini-Change
Right Trunk Gender	Male
Temperature Range - Operating	-20°C to +80°C

This document was generated on Sep 26, 2023