



Part Number : [1204800462](#)
Product Description : Brad M23 Power Single-Ended Cordset, 8 Poles, Female (Straight) to Pigtail, 19/16 AWG, WSOR Cable, 3.0m (9.84') Length
Series Number : 120480
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Number : K0P8S00W03M030



Documents & Resources

- Drawings**
[Drawing 1204800462_sd.pdf](#)
- 3D Models and Design Files**
[3D Model 1204800462_stp.zip](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120480
Description	Brad M23 Power Single-Ended Cordset, 8 Poles, Female (Straight) to Pigtail, 19/16 AWG, WSOR Cable, 3.0m (9.84') Length
Comments	WSOR Cable Jacket
IP Rating	IP67
Product Family	Brad M23 Signal and Power Connectors
Product Name	Brad M23
Protocol	N/A
Type	Single Ended
UPC	889056617468

Electrical

Current - Maximum per Contact	12.0A, 18.0A
Voltage - Maximum	300V / 600V

Physical

Cable Diameter	12.10mm (.480")
Cable Length	3.0m (9.84')
Color - Cable Jacket	Orange
Connector End A	M23
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Multiple
LED Indicator	No
Material - Cable Jacket	TPU
Material - Connector Body	TPU

Material - Contact	Copper Alloy
Material - Coupling Nut	Brass
Material - Plating Mating	Gold
Orientation	Straight to Pigtail
Poles	8
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	WSOR
Wire Size (AWG)	16, 19

Mates With / Use With

Mates with Part(s)

Description	Part Number
Brad M23 Signal Connectors	<u>120233</u>
Brad M23 Signal Connectors	<u>120234</u>