



Part Number : [1210503392](#)

Product Description : mPm DIN Valve Connector, Form B - 11mm, 2 Pole Plus Ground, PUR UL Cable Pigtail, Yellow LED, Black Nitrile Gasket, 115V

Series Number : 121050

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Number : E462B2A50021S0L



Documents & Resources

Drawings

[Drawing 1210503392_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead Oxide; Lead per per D(2020)9139-DC (19 Jan 2021)
EU RoHS	Compliant with Exemption 7(c)-I per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	121050
Description	mPm DIN Valve Connector, Form B - 11mm, 2 Pole Plus Ground, PUR UL Cable Pigtail, Yellow LED, Black Nitrile Gasket, 115V
IP Rating	IP65
Product Family	mPm DIN Valve Connectors
Product Name	mPm
Protocol	N/A
Region	America, Europe
Type	Single Ended
UPC	78172534604

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	115V

Physical

Cable Diameter	5.72mm (.225")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Connector End A	Brad mPm DIN B - 11mm
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	None
LED Indicator	Yellow
Material - Cable Jacket	PUR UL
Material - Connector Body	Polypropylene
Material - Contact	Brass

Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Net Weight	185.000/g
Orientation	90° to Pigtail
Poles	2
Temperature Range - Operating	-40° to +90°C
Wire/Cable Type	N/A
Wire Size (AWG)	20

This document was generated on Sep 26, 2023