




Part Number : [1300138076](#)
Product Description : Mini-Change Receptacle,
5 Poles, 1/2" - 14 NPT Threads, Female
(Straight) to 16 AWG Leads, 1.0m (3.28')
Length
Series Number : 130013
Status : Active
Product Category : Circular Industrial
Connectors
Engineering Number : 1R5000A80M010



Documents & Resources

Drawings
[Drawing 1300138076_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

ZZCERT_CE - Declaration of Conformity : CER_4000408919_00_000.pdf

ZZCERT_UKCA - Declaration of Conformity : CER_4000410299_00_000.pdf

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	130013
Description	Mini-Change Receptacle, 5 Poles, 1/2" - 14 NPT Threads, Female (Straight) to 16 AWG Leads, 1.0m (3.28') Length
IP Rating	IP67
Product Family	Brad Mini-Change Connectors
Product Name	Mini-Change
Type	Single Ended (pigtail)
UPC	887191262659

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	300V AC/DC

Physical

Coupling Type	Internal Thread
Gender	Female
Keyway	Single
Length	1.0m
Material - Component	Nickel-plated Zinc Die-Cast
Mounting Thread Size	1/2" - 14 NPT
Net Weight	162.050/g
Orientation	Straight
Panel Mount	Front
Poles	5

Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	UL 1015
Wire Size (AWG)	16