



Part Number : [1301460023](#)

Product Description : Watertite Extreme Plug, 2 Pole/3 Wire, NEMA 5-20, 125V, Cord Grip Body Size F2, Black, Silicone Husk

Series Number : 130146

Status : Active

Product Category : Wiring Devices

Engineering Number : 14W33BLK



Documents & Resources

Drawings

[Drawing 1301460023_sd.pdf](#)

3D Models and Design Files

[3D Model 1301460023_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Not Reviewed per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Wiring Devices
Series	130146
Description	Watertite Extreme Plug, 2 Pole/3 Wire, NEMA 5-20, 125V, Cord Grip Body Size F2, Silicone Husk
IP Rating	IP69K
NEMA Configuration	NEMA 5-20
Product Family	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Specialty	N/A
Type	Plug
UPC	78678871022

Agency

CSA	LR6837
UL	E10176

Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	125V

Physical

Cord Grip Body Size	F2 1/2"
Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Male

Length	N/A
Lighted Connector	No
Locking Blade	No
Net Weight	126.098/g
Poles	2-pole/3-wire
Receptacle Type	N/A

This document was generated on Sep 26, 2023