



Part Number : [1301460041](#)


Product Description : Watertite Extreme Extra Hard Outdoor Plug, 2 Pole/3 Wire, NEMA 6-20, 250V, Cord Grip Body Size F2, Black, Silicone Husk

Series Number : 130146

Status : Active

Product Category : Wiring Devices

Engineering Number : 14W48BLK



Documents & Resources

Drawings

[Drawing 1301460041_sd.pdf](#)

3D Models and Design Files

[3D Model 1301460041_stp.zip](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Wiring Devices
Series	130146
Description	Watertite Extreme Extra Hard Outdoor Plug, 2 Pole/3 Wire, NEMA 6-20, 250V, Cord Grip Body Size F2, Black, Silicone Husk
IP Rating	IP69K
NEMA Configuration	NEMA 6-20
Product Family	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Specialty	N/A
Type	Plug
UPC	78678871049

Agency

CSA	LR6837
UL	E10176

Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	250V

Physical

Cord Grip Body Size	F2 1/2"
Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Male
Length	N/A

Lighted Connector	No
Locking Blade	No
Poles	2-pole/3-wire
Receptacle Type	N/A

This document was generated on Sep 26, 2023