



Part Number : [1301460053](#)

Product Description : Watertite Extreme Extra-Hard Outdoor use Connector, 2 Pole/3 Wire, NEMA 5-20, 125V, Cord Grip Body Size F2, Black, Silicone Husk

Series Number : 130146

Status : Active

Product Category : Wiring Devices

Engineering Number : 15W33BLK



---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Wiring Devices

Series	130146
Description	Watertite Extreme Extra-Hard Outdoor use Connector, 2 Pole/3 Wire, NEMA 5-20, 125V, Cord Grip Body Size F2, Black, Silicone Husk
IP Rating	IP69K
NEMA Configuration	NEMA 5-20
Product Family	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Specialty	N/A
Type	Connector
UPC	78678875352

#### Agency

CSA	LR6837
UL	E10176

#### Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	125V

#### Physical

Cord Grip Body Size	F2 1/2"
Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	No
Poles	2-pole/3-wire
Receptacle Type	Single

---



---

This document was generated on Sep 26, 2023